

Osmos Soft Water Cabinet Glasswash

Description

For use in enclosed cabinet auto-glass washing machines. Suitable for soft water areas. Use in conjunction with Cleenol Universal Glass & Dishwasher Rinseaid to enhance the visual quality of the cleaned glasses. Specially designed for use through automatic dosing systems. Safe to use on all glasses.

Contains no caustic, responsible for the etching of glassware. Effectively removes soiling, including lipstick, without affecting beer head retention.

Directions For Use

Designed to be used through an automatic dosing system, where a Cleenol engineer will set the dose rate. Always use with Cleenol Rinseaid. Do not use for hand dishwashing.

Product Codes

OSM-SWCG-2X5



Storage

Store in cool conditions away from direct sources of heat. Avoid extremes of temperature. Do not allow to freeze. Ensure the cap is tightly fitted after use. Keep out of reach of children.

Shelf Life

Shelf life 24 months, if stored as recommended. Use within 6 months of opening.

Environmental

Do not allow large quantities of neat liquid to enter surface waterways. This product uses recyclable packaging. None of the components of this product are animal derived.

Notes

It contains no Phosphates or NTA.

Cleenol Group Ltd

Registered address: Beaumont Road, Banbury, Oxon, OX16 1RB, UK.

Tel: +44 (0) 1295 251721 | Email: sales@cleenol.co.uk | Web: www.cleenol.com

Cleenol Group Ltd is a limited company registered in England & Wales under N° 00635803

